

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Bus system T-connector, DeviceNet™, 5-position, unshielded, Plug straight 7/8"-16UNF, on Socket straight 7/8"-16UNF and Socket straight 7/8"-16UNF, Parallel distributor



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 542616
GTIN	4046356542616
Weight per Piece (excluding packing)	98.700 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 80 °C (Plug / socket)

#### General data

Rated current at 40°C	10 A (at 25 °C)
Rated voltage	63 V DC
Number of positions	5
Signal type/category	DeviceNet™
Overvoltage category	II
Degree of pollution	3
Alternative short product description	T distributor
Contact material	CuZn
Contact carrier material	PA

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029

### Technical data

#### General data

Contact surface material	AU
--------------------------	----

#### Characteristics head 2

Color	black
-------	-------

#### Standards and Regulations


Flammability rating according to UL 94	HB
--	----

#### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings


Dimensional drawing



T-distributor 7/8", top view

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029


Circuit diagram



Contact assignment of the 7/8" T-distributor

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029


Schematic diagram



Pin assignment, plug, 7/8"-16UNF, 5-pos., view of male side

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029

Schematic diagram



Pin assignment, socket, 7/8"-16UNF, 5-pos., view of female side

### Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102
eCl@ss 9.0	27440106

# Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029

## Classifications

### ETIM

ETIM 2.0	EC000830
ETIM 3.0	EC001855
ETIM 4.0	EC000421
ETIM 5.0	EC002635
ETIM 6.0	EC002925
ETIM 7.0	EC002925

### UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	39121413
UNSPSC 19.0	31251501
UNSPSC 20.0	31251501
UNSPSC 21.0	31251501

## Approvals


### Approvals

#### Approvals

UL Listed / UL Listed / EAC

#### Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 221474
Nominal voltage UN	250 V		
Nominal current IN	8 A		

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 221474
-----------	---	---	---------------

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029

### Approvals

EAC



RU C-  
DE.BL08.B.00511

### Accessories

#### Accessories

##### Plug for cable screw gland

Screw plug - PROT-MINMS-PA-CHAIN - 1430925

7/8" sealing cap made of plastic with fixing band, for sensor cables, for 7/8" sockets



##### Protective cap

Sealing cap - PROT-MINFS-PA-CHAIN - 1430912

7/8" sealing cap made of plastic with fixing band, for sensor cables, for 7/8" connectors



##### Screwdriver tools

Tool - SAC BIT MIN-D25 - 1212512

Nut for assembling 7/8" connectors with a knurl diameter of 25 mm, with 4 mm hexagonal drive



Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

##### Terminal marking

## Bus system T-connector - SAC-5P-MINT/2XMIN DN - 1401029

### Accessories

Zack Marker strip, flat - ZBF 17:UNBEDRUCKT - 0815020



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 17 mm, lettering field size: 17 x 5.2 mm, Number of individual labels: 5

---

### Torque tool

Torque screwdriver - TSD 08 SAC - 1212597



Torque screw driver with preset torque of 0.8 Nm, with 4 mm hexagon for accommodating SAC bits, two-component handle with non-slip grip

---

Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm