

Memory - CF FLASH 256MB PDPI BASIC - 2700549

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory, plug-in, 256 MB with license key for licensing the PDPI - BASIC function block for precise multi-channel controllers with self-optimization, additional functions: e.g., for heating and cooling functions or hydraulic movements.

Product Description

Program and configuration memory for storing application programs and other files in the file system of the PLC, with license key for the function block libraries.

The function blocks for the PDPI controllers from Phoenix Contact are licensed, i.e., a fee is charged for each controller on which blocks subject to a license are to be used. During runtime the blocks check the license stored in the controller and are then enabled or can be used for a limited time in demo mode.

Please observe the specified performance data of your controller(s) and check that they are suitable for your application.


For users who do not use the function block libraries, the program and configuration memory is also available without a license as an option.

Your advantages

- ✓ Program and configuration memory, plug-in
- ✓ For storing application programs and other files in the file system of the PLC
- ✓ License key for licensing the PDPI - BASIC functional block



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 575782
GTIN	4046356575782
Weight per Piece (excluding packing)	15.000 g
Custom tariff number	85235190
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	42.8 mm
--------	---------

Memory - CF FLASH 256MB PDPI BASIC - 2700549

Technical data

Dimensions

Depth	3.3 mm
Width	36.4 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Weight	9 g
Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	27242200
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

ETIM

ETIM 3.0	EC000192
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606

Memory - CF FLASH 256MB PDPI BASIC - 2700549

Classifications

UNSPSC

UNSPSC 21.0	32101606
-------------	----------

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	--	---------------
