

# Protective hose fixing bracket - WP-BASE A M20 - 3241084


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fixing bracket for protective sleeves, fixed with two screws



## Key Commercial Data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 712279
GTIN	4046356712279
Weight per Piece (excluding packing)	28.280 g
Custom tariff number	73269098
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Hole diameter	21 mm
---------------	-------

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 200 °C
---------------------------------	-------------------

### General

Color	silver
Components	halogen-free
Material	Steel, galvanized

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Protective hose fixing bracket - WP-BASE A M20 - 3241084

### Classifications

#### eCl@ss

eCl@ss 10.0.1	23159090
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439202
eCl@ss 8.0	27439202
eCl@ss 9.0	23159090

#### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC002498
ETIM 5.0	EC001458
ETIM 6.0	EC001458
ETIM 7.0	EC001458

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411
UNSPSC 18.0	31162906
UNSPSC 19.0	31162906
UNSPSC 20.0	31162906
UNSPSC 21.0	31162906