

## Cable feed-through plates - MH-27-MULTI-65-PV-BK - 1424583

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable feed-through plates, no. of conductors: 27, length: 154 mm, width: 56 mm, height: 18.5 mm, external cable diameter: 26x 3 mm ... 6 mm , color: black

### Your advantages

- The panel cutouts of size B24 heavy-duty connectors can be used.

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 374864
GTIN	4055626374864
Weight per Piece (excluding packing)	76.700 g
Custom tariff number	39269097
Country of origin	Finland

### Technical data

#### Dimensions

Length	154 mm
Width	56 mm
Height	18.5 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm
External cable diameter	26x 3 mm ... 6 mm
	1x 10 mm ... 20 mm

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 90 °C

#### General

## Cable feed-through plates - MH-27-MULTI-65-PV-BK - 1424583

### Technical data

#### General

No. of conductors	27
Material	TPE-SEBS
	PP (Core)
	TPE-SEBS (external material)
Flammability rating according to UL 94	V0
Color	black
Note	incl. mounting screws
Installation instructions	M4 mounting screw, torque: 1.8 Nm, SW5 Allen key
	The mounting screws included should be used for assembly.  Assembly steps: 1) Fix Multigates with the mounting screws provided (observe torque) 2) Make a hole in the membrane (with a screwdriver) or cut off the tip of the cone 3) Guide the cable through the opening (from the outside). Withdraw the cable approximately 20 mm (to improve strain relief).

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings



# Cable feed-through plates - MH-27-MULTI-65-PV-BK - 1424583

Dimensional drawing



Wall cutout drawing

## Classifications

eCl@ss

eCl@ss 5.1	23110102
eCl@ss 6.0	27409200
eCl@ss 7.0	27409208
eCl@ss 8.0	27409208
eCl@ss 9.0	27400569

ETIM

ETIM 5.0	EC001004
ETIM 6.0	EC001004
ETIM 7.0	EC001004

## Approvals

Approvals

## Cable feed-through plates - MH-27-MULTI-65-PV-BK - 1424583

### Approvals

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

---