

PRODUCT-DETAILS

216P6W

Ind. P&S#216P6W



General Information

Extended Product Type	216P6W
Product ID	2CMA166460R1000
EAN	7392696664608
Catalog Description	Ind. P&S#216P6W
Long Description	Plug, earthing sleeve position 6h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue

Ordering

E-Number (Sweden)	E2416237
E-Number (Finland)	2421632
E-Number (Norway)	2416237
EAN	7392696664608
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	70 mm
Product Net Height	70 mm

Product Net Length	128 mm
Product Net Depth / Length	128 mm
Product Net Weight	0.18 kg

Container Information

Package Level 1 Width	95 mm
Package Level 1 Depth / Length	95 mm
Package Level 1 Height	175 mm
Package Level 1 Gross Weight	0.186 kg
Package Level 1 EAN	7392696664608
Package Level 1 Units	box 1 piece
Package Level 2 Units	400 piece

Technical UL/CSA

Tightening Torque UL/CSA	7.1 in-lb
-----------------------------	-----------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1025779
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1 ... 2.5 mm ²
Cable Diameter	6 ... 13 mm
Cable Entry Position	Anti-kink sleeve
Color	Blue
Connection Type	Screw Clamp
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Plug
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#216P6W

Material	Plastic
Number of Poles	3
Order Multiple	1 piece
Product Main Type	TP
Product Name	Industrial Plug
Protection Type	Watertight
Rated Current (I_n)	16 A
Rated Voltage (U_r)	200 ... 250 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Plugs
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700002D0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440501
UNSPSC	39121402

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Plugs

