

## Display Adapters & Convertors

### DisplayPort Adapters

Part No: 2409EMH

This high quality adaptor supports the link from a PC featuring the Mini DisplayPort interface to a HDMI display.



#### Specification

● <b>Input</b>	<b>Output</b>
Mini DisplayPort M	HDMI F
Max 1920x1200	Max 1920x1200
● <b>Operating Frequency</b>	
Vertical Frequency Range	50/60Hz
	162Mhz
Bandwidth	225MHz/2.25 Gbps / channel
● <b>Physical</b>	
Size (LxWxD)	45 x 45 x 12mm
Weight (Net)	19g
Colour	White
Connector	Nickel Plated
● <b>Operational</b>	
Operating Temperature	0 °C to +55 °C
Operating Humidity	10% to 85% RH (no condensation)
Storage Temperature	0 °C to +70 °C
Storage Humidity	5% to 90% RH (no condensation)
● <b>Power Requirement</b>	
	No external power needed
● <b>Regulatory Approvals</b>	
	CE, FCC, RoHS

#### Features & Benefits

- Complies with DisplayPort 1.1 standard
- Supports HDMI resolution up to 1080P
- Supports extend/mirror display
- Easy to use adapter, no software required
- POWERED from mini DisplayPort
- Plug-n-Play

#### Ordering Information

- **Part No:**  
2409EMH
- **Product Description:**  
VIDEK Mini DisplayPort Plug to HDMI Socket Adaptor - White

# VIDEK

## Display Adapters & Convertors DisplayPort Adapters

Part No: 2409EMH

