

Han DD double module, crimp female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 036 3102
Specification	Han DD double module, crimp female
HARTING eCatalogue	https://b2b.harting.com/09140363102

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han DD® module

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	36
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance

Material properties

Colour (insert) RAL 7032 (pebble grey)

Material flammability class acc. to UL 94 V-0

Specifications and approvals

Specifications EN 60664-1
IEC 61984

Commercial data

Packaging size 1

Net weight 21.5 g

Country of origin China

European customs tariff number 85389099

eCl@ss 27440217 Module for industrial connectors (power/signals)