




### MS44-18G

This compact unit is a true 4K, 4x4 matrix, allowing any source to simultaneously display to any of its four outputs. The versatile MS44-18G also combines digital audio de-embedding, EDID control, IR, LAN and RS232 connectivity.

### FEATURES

- 4 x HDMI 2.0 Inputs /Outputs
- 4 x de-embedded S/PDIF Audio Output
- Supports 4K2K60Hz YU4:4:4
- Bandwidth up to 18Gbps
- Compliant to HDCP 2.2 and HDCP -1.4 (Output follows Input)
- Supports HDR10 and 3D
- Supports Dolby True HD and DTS -HD master Audio
- Controllable from Front Panel IR, RS232, IP and Web Interface
- Flexible and affordable distribution switching platform
- EDID Management



### SPECIFICATIONS

<b>PART NUMBER</b>	SY-MS44-18G	
<b>VIDEO RESOLUTIONS/FORMATS</b>	480i/576p/720i/720p/1080i/1080p/3840x2160 (8 to 16bit 24 to 60Hz 4:2:0 to 4:4:4)	
<b>BANDWIDTH</b>	18Gbps	
<b>HDCP</b>	Compatible with all versions up to 2.2v	
<b>INPUTS</b>	<b>Video</b> 4x HDMI type A 2.0v	
<b>OUTPUTS</b>	<b>Video</b> 4x HDMI type A 2.0v	<b>Audio</b> 8x digital de embedding (Phoenix sockets)
<b>CONTROL</b>	<b>IR</b> Receiver Input via 3.5mm R Handset	<b>RS232</b> 57600 baud, 8 data bits, no parity, 1 stop bit and no handshaking
<b>CLOCK SPEED</b>	600Mhz	
<b>LAN</b>	Via RJ45	
<b>POWER SUPPLY</b>	5V DC, 3.0A	
<b>WEIGHT AND DIMENSIONS</b>	<b>Weight (net)</b> 0.750kg	<b>Size (WHD)</b> 216 x 34 x 105mm (Without rack mounted ears and other connectors)
<b>WHAT'S IN THE BOX</b>	1x 4x4 Matrix 1x 12V 5A external power supply 1x 0.5m UK power plug 1x Phoenix plug (Connection for RS232 port) 2x rack ears with 6 chassis screws 1x IR handset 1x IR Receiver 1x mini CD containing LAN Control drivers and manuals	

Developer member HDBaseT alliance. "HDMI, the HDMI Logo, and High-Definition Multimedia Interface are trademarks or registered trademarks of the HDMI Licensing LLC in the United States and other countries" Details subject to change with no prior notice.