



Main

Range	TeSys
Accessory / separate part category	Protection accessory
Product or component type	Current limiting module
Function of module	Increasing the breaking capacity of a circuit breaker
Range compatibility	TeSys GV2
Product compatibility	GV2RT GV2ME GV2P GV2L
Mounting location	On top of the circuit breaker
[Ie] rated operational current	32 A
[Ith] conventional free air thermal current	63 A conforming to IEC 60947-1
Operating threshold	1500 A
Breaking capacity	<= 100 kA depending on protective device
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-1

Complementary

Connections - terminals	Screw clamp terminals 1 x 1.5...25 mm ² rigid Screw clamp terminals 2 x 1.5...10 mm ² rigid Screw clamp terminals 1 x 1.5...25 mm ² flexible without cable end Screw clamp terminals 2 x 1.5...10 mm ² flexible without cable end Screw clamp terminals 1 x 1.5...16 mm ² flexible with cable end Screw clamp terminals 2 x 1.5...4 mm ² flexible with cable end
Tightening torque	2.2 N.m
Net weight	0.13 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Current Limiter

GV1L3

