

PRODUCT-DETAILS

463MVS6WH

Switched interlocked socket-outlet, vertical,
Heavy Duty, 6h, 63A, IP67, 3P+N+E



General Information

Extended Product Type	463MVS6WH
Product ID	2CMA162845R1000
EAN	7392696628457
Catalog Description	Switched interlocked socket-outlet, vertical, Heavy Duty, 6h, 63A, IP67, 3P+N+E
Long Description	Switched Interlocked Socket Outlet, vertical, Heavy Duty, earthing sleeve position 6h, rated current 63A, IP67 watertight, 3-poles+neutral+earth

Ordering

E-Number (Sweden)	E2417031
E-Number (Finland)	2420299
E-Number (Norway)	2417031
EAN	7392696628457
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	175 mm
Product Net Height	149 mm

Product Net Length	463 mm
Product Net Depth / Length	463 mm
Product Net Weight	2.5 kg

Container Information

Package Level 1 Width	262 mm
Package Level 1 Depth / Length	492 mm
Package Level 1 Height	182 mm
Package Level 1 Gross Weight	2.5 kg
Package Level 1 EAN	7392696628457
Package Level 1 Units	box 1 piece
Package Level 2 Units	28 piece

Technical UL/CSA

Ampere Rating UL/CSA	60 A
Tightening Torque UL/CSA	31 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1506655
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	6 ... 25 mm ²
Cable Diameter	17 ... 35 mm
Cable Entry Position	Knock-out on Top and drill marks down
Cable Outlets Per Side	1xØ40+1xØ50 mm on top and drill marks on bottom
Color	Red
Connection Type	Screw
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Switched Interlocked Socket outlet, vertical, Heavy Duty

Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#463MVS6WH
Material	Plastic
Mounting Holes	378x145, 128x145
Mounting Type	Vertical
Number of Auxiliary Contacts NO	1
Number of Poles	5
Order Multiple	1 piece
Product Main Type	CMVS
Product Name	Industrial Switched Interlocked Socket Outlet
Protection Type	Switched Interlocked
Rated Current (I_n)	63 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2, -4
Sub-Function	Cable entry, knock-outs Ø40+50mm on top and drill marks on bottom
Suitable For	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000043M0001
Installation Manual	2CMC000043M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39120000

Technical

Wire Size	8 ... 4 AWG
Tightening Torque	3.5 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Switched Interlocked Socket Outlets

