
PRODUCT-DETAILS

416MHS6

Switched interlocked socket-outlet, 6h, 16A,
IP44, 2P+N+E



General Information

Extended Product Type	416MHS6
Product ID	2CMA167640R1000
EAN	7392696676403
Catalog Description	Switched interlocked socket-outlet, 6h, 16A, IP44, 2P+N+E
Long Description	Switched Interlocked Socket Outlet, horizontal, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416825
E-Number (Finland)	2421379
E-Number (Norway)	1564817
EAN	7392696676403
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	168 mm
Product Net Height	116 mm

Product Net Length	129 mm
Product Net Depth / Length	129 mm
Product Net Weight	0.7 kg

Container Information

Package Level 1 Width	135 mm
Package Level 1 Depth / Length	140 mm
Package Level 1 Height	200 mm
Package Level 1 Gross Weight	0.7 kg
Package Level 1 EAN	7392696676403
Package Level 1 Units	box 1 piece
Package Level 2 Units	174 piece

Technical UL/CSA

Ampere Rating UL/CSA	20 A
Tightening Torque UL/CSA	7.1 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1515100
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	13 ... 17 mm
Cable Entry Position	Top and bottom
Cable Outlets Per Side	1xØ32
Color	Red
Connection Type	Screw
Degree of Protection	IP44
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Switched interlocked socket outlet, horizontal
Housing Material	Thermoplastic (PBT)

Invoice Description	Ind. P&S#416MHS6
Material	Plastic
Mounting Holes	146x91
Mounting Type	Horizontal
Number of Poles	5
Order Multiple	1 piece
Product Main Type	CMHS
Product Name	Industrial Switched Interlocked Socket Outlet
Protection Type	Switched Interlocked
Rated Current (I_n)	16 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2, -4
Sub-Function	Cable entry, knock-outs Ø25mm/M25
Suitable For	Switched Interlocked Socket Outlets, Horizontal
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000032M0001
Installation Manual	2CMC000032M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39121406

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Switched Interlocked Socket Outlets

