
PRODUCT-DETAILS

432MVS6

Switched interlocked socket-outlet, 6h, 32A, IP44, 3P+N+E



General Information

Extended Product Type	432MVS6
Product ID	2CMA167709R1000
EAN	7392696677097
Catalog Description	Switched interlocked socket-outlet, 6h, 32A, IP44, 3P+N+E
Long Description	Switched Interlocked Socket Outlet, vertical, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416863
E-Number (Finland)	2421402
E-Number (Norway)	1543853
EAN	7392696677097
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	120 mm
Product Net Height	149 mm

Product Net Length	235 mm
Product Net Depth / Length	235 mm
Product Net Weight	1.04 kg

Container Information

Package Level 1 Width	152 mm
Package Level 1 Depth / Length	120 mm
Package Level 1 Height	265 mm
Package Level 1 Gross Weight	1.15 kg
Package Level 1 EAN	7392696677097
Package Level 1 Units	box 1 piece
Package Level 2 Units	125 piece

Technical UL/CSA

Ampere Rating UL/CSA	30 A
Tightening Torque UL/CSA	10.6 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000057M0000
RoHS Information	2CMC700005D0001
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm ²
Cable Diameter	13 ... 21.5 mm
Cable Entry Position	Top
Cable Outlets Per Side	1xØ25
Color	Red
Connection Type	Screw
Degree of Protection	IP44
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Switched interlocked socket outlet, vertical
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#432MVS6

Material	Plastic
Mounting Holes	171x90
Mounting Type	Vertical
Number of Poles	5
Order Multiple	1 piece
Product Main Type	CMVS
Product Name	Industrial Switched Interlocked Socket Outlet
Protection Type	Switched Interlocked
Rated Current (I_n)	32 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2, -4
Sub-Function	Cable entry, knock-outs Ø25mm
Suitable For	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000030M0001
Installation Manual	2CMC000030M0001
RAL Number	RAL 7001 - Silver Grey

Classifications

eClass	27440510
UNSPSC	39121406

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Critical & Safe → Switched Interlocked Socket Outlets

