

PRODUCT-DETAILS

# M2M LV

## M2M LV Network analyser



### General Information

Extended Product Type	M2M LV
Product ID	2CSG299943R4052
EAN	8012542999430
Catalog Description	M2M LV Network analyser
Long Description	M2M is a network analyser with 2 digital outputs, aux supply 24- 230 V a.c./d.c.

### Technical

Meter Type	Digital
Mounting Type	Front-panel
Dimensions	96 mm x 96 mm
Rated Operational Voltage	10 ... 500 V AC
Options Provided	Total harmonic distortion (THD)
I/O Option	2 digital output
Power Loss	at Rated Operating Conditions per Pole 7 W

### Environmental

Ambient Air Temperature	Operation -5 ... +55 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

## Dimensions

Product Net Width	0.096 m
Product Net Height	0.096 m
Product Net Depth / Length	77 mm
Product Net Weight	0.300 kg

---



---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.11 m
Package Level 1 Height	0.23 m
Package Level 1 Depth / Length	0.155 m
Package Level 1 Gross Weight	0.5 kg
Package Level 1 EAN	8012542999430

---



---

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	90303100
Replacement Product ID (NEW)	2CSG251151R4051

---



---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5710
Environmental Information	See RoHS Information
Instructions and Manuals	2CSG445010D1002
RoHS Information	2CSC445023K2703

---



---

## Popular Downloads

Data Sheet, Technical Information	9AKK107046A0430
Instructions and Manuals	2CSG445010D1002

---



---

## Classifications

Object Classification Code	P
ETIM 4	EC001194 - Power quality analyzer
ETIM 5	EC001194 - Power quality analyzer
ETIM 6	EC001194 - Power quality analyzer
ETIM 7	EC001194 - Power quality analyser

---

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Energy Efficiency Devices → Network Analyzers and Multimeters

