
Hand slide valve VBOH-32-G38 Part number: 1482679

FESTO





| Feature | Value |
|--|--|
| Type code | VBOH |
| Valve function | 3/2, bistable |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G3/8 |
| Actuation type | Manual |
| Type of mounting | Screw-in Line installation |
| Standard nominal flow rate | 2201 l/min |
| Nominal width | 9.9 mm |
| Operating pressure | -0.95 bar 12 bar |
| Ambient temperature | -10 ℃ 80 ℃ |
| Housing material | Wrought aluminum alloy Anodized |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Width dimension | 39.5 mm |
| Sealing principle | Soft |
| Mounting position | Any |
| Design | Sleeve gate valve |
| Type of control | Direct |
| Symbol | 00991286 |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Temperature of medium | -10 °C 80 °C |
| Actuating force | 41 N |
| Product weight | 70 g |
| Material of screwed trunnion | Anodized Wrought aluminum alloy |
| Note on materials | RoHS-compliant |
| Seals material | NBR |