

N150 Wireless Nano USB Adapter


Model: MW150US

// Highlights

- Compact, convenient solution to make your device wireless
- Perfect for essential Internet applications such as web browsing, email, and chatting
- Supports Windows 8.1/8/7/XP (32/64bit)



// Connections



// Specifications

Physical Specifications

Interface
USB 2.0

Dimensions (W x D x H)
18.9x14.8x6.85 mm

Antenna
Internal

Wireless Specifications

Wireless Standards	Frequency	EIRP	Wireless Security	Wireless Function
IEEE 802.11b/g/n	2.4-2.4835GHz	<20dBm (EIRP)	WEP, WPA/WPA2, WPA-PSK/WPA2-PSK	Enable/Disable Wireless Radio, Wireless Statistics

Signal Rate

- 11n: Up to 150Mbps (Dynamic)
- 11g: Up to 54Mbps (Dynamic)
- 11b: Up to 11Mbps (Dynamic)

Reception Sensitivity

- 130M: -65dBm@10% PER
- 108M: -68dBm@10% PER
- 54M: -68dBm@10% PER

- 11M: -85dBm@8% PER
- 6 M: -88dBm@10% PER
- 1 M: -90dBm@8% PER

// Package Contents

1. N150 Wireless Nano USB Adapter (MW150US)
2. Quick Installation Guide
3. Resource CD



For more information, please visit
www.mercusys.com

MERCUSYS TECHNOLOGIES CO., LTD.
3rd Floor, Building R1-B, No. 23, Gaoxin 4th Road,
South Hi-Tech Park, Nanshan, Shenzhen, P.R.China

Specifications are subject to change without notice. MERCUSYS is a registered trademark of MERCUSYS TECHNOLOGIES CO., LTD. Other brands and product names are trademarks or registered trademarks of their respective holders.
Copyright © 2016 MERCUSYS TECHNOLOGIES CO., LTD. All rights reserved.