

Solenoid coil VACF-A-A1-1

Part number: 8030822

FESTO



Data sheet

Feature	Value
Type code	VACF
Maritime classification	See certificate
Mounting position	Any
Duty cycle	100%
Insulation class	H
Coil characteristics	24 V DC: 2.6 W
Permissible voltage fluctuations	+/- 10 %
Certificate issuing authority	DNVGL-TAA000011J
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Certification	c UL us - Recognized (OL)
Electrical connection	as per EN 175301-803 Form A
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Thermoplastic Steel
Material of winding	Copper