

Acer H6531BD(MR.JR211.002)

Acer H6531BD - DLP projector - portable - 3500 lumens - Full HD (1920 x 1080) - 16:9 - 1080p



## Main Specifications

Product Description	Acer H6531BD - DLP projector - portable
Device Type	DLP projector - 1080p
Brightness	3500 lumens
Contrast Ratio	10000: 1
Resolution	Full HD (1920 x 1080)
Native Aspect Ratio	16:9
Colour Support	1.07 billion colours (30-bit)
Bulb type	203 Watt
Bulb life cycle	Up to 5000 hour(s) - normal mode ; Up to 10000 hour(s) - economic mode ; Up to 20000 hour(s) - extreme economic mode
Video Input	(NTSC, SECAM, PAL)
Speakers	Speaker(s) - integrated
Power	AC 120/230 V
Power Consumption Operational	270 Watt
Weight	2.6 kg

## Extended Specification

### General

Device Type	DLP projector - 1080p
-------------	-----------------------

### Projector

Brightness	3500 lumens
Contrast Ratio	10000: 1
Image Size	68.58 cm - 762 cm
Projection Distance	1 m
Throw Ratio	1.5 - 1.65: 1
Digital Zoom Factor	2x
Resolution	Full HD - Full HD (1920 x 1080) (native) / 1920 x 1200 (resized)
Native Aspect Ratio	16:9
Colour Support	1.07 billion colours (30-bit)
Max Sync Rate (V x H)	120 Hz x 100 kHz
Bulb type	203 Watt

Bulb life cycle	Up to 5000 hour(s) - normal mode Up to 10000 hour(s) - economic mode Up to 20000 hour(s) - extreme economic mode
-----------------	--

Features 4:3 aspect ratio support

#### Lens

Focus Type	Manual
Lens Aperture	F/2.0-2.05
Zoom Type	Manual
Zoom Factor	1.1x
Keystone Correction Direction	Vertical
Vertical Keystone Correction	-40 / +40

#### Video Input

TV System	NTSC, SECAM, PAL
Video Interfaces	VGA, HDMI, component video

#### Speakers

Type	Integrated
Sound Output Mode	Mono
Output Power / Channel	3 Watt
Speakers	1 x mixed channel

#### Expansion / Connectivity

Interfaces	1 x VGA / component video input - 15 pin HD D-Sub (HD-15) 2 x HDMI - 19 pin HDMI Type A 1 x VGA output - 15 pin HD D-Sub (HD-15) 1 x USB - 4 pin USB Type A 1 x audio line-out 1 x audio line-in
------------	---

#### Miscellaneous

Included Accessories Wireless remote control

#### Power

Power Source	AC
Nominal Voltage	AC 120/230 V
Power Consumption Operational	270 Watt

#### Dimensions & Weight

Weight 2.6 kg

#### Environmental Parameters

Min Operating Temperature	0 °C
Max Operating Temperature	40 °C
Humidity Range Operating	0 - 80%

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet