

Acer X138WHP(MR.JR911.00Z)

Acer X138WHP - DLP projector - UHP - portable - 3D - 4000 lumens - WXGA (1280 x 800) - 16:10 - 720p



## Main Specifications

Product Description	Acer X138WHP - DLP projector - portable - 3D
Device Type	DLP projector - 720p
3D Capable	Yes (3D glasses sold separately)
Built-in Devices	Speaker
Localisation	United Kingdom,Europe
Brightness	4000 lumens
Contrast Ratio	20000:1 (dynamic)
Resolution	WXGA (1280 x 800)
Native Aspect Ratio	16:10
Colour Support	1.07 billion colours (30-bit)
Bulb type	UHP 220 Watt
Bulb life cycle	Up to 6000 hour(s) - normal mode   Up to 10000 hour(s) - economic mode   Up to 15000 hour(s) - extreme economic mode
Video Input	(NTSC, SECAM, PAL)
Speakers	Speaker(s) - integrated
Power	AC 120/230 V
Power Consumption Operational	275 Watt
Dimensions (WxDxH)	31.3 cm x 24 cm x 11.37 cm
Weight	2.7 kg
Manufacturer Warranty	2-year warranty

## Extended Specification

### General

Device Type	DLP projector - 720p
3D Capable	Yes (3D glasses sold separately)
Built-in Devices	Speaker
Localisation	United Kingdom,Europe

### Projector

Brightness	4000 lumens
Contrast Ratio	20000:1 (dynamic)
Image Size	68.58 cm - 762 cm

Projection Distance	1 m - 10 m
Throw Ratio	1.54 - 1.72:1
Digital Zoom Factor	2x
Resolution	WXGA - WXGA (1280 x 800) (native) / 1920 x 1200 (resized)
Native Aspect Ratio	16:10
Colour Support	1.07 billion colours (30-bit)
Max Sync Rate (V x H)	120 Hz x 100 kHz
Bulb type	UHP 220 Watt
Bulb life cycle	Up to 6000 hour(s) - normal mode Up to 10000 hour(s) - economic mode Up to 15000 hour(s) - extreme economic mode
Features	16:9 aspect ratio support, 4:3 aspect ratio support, Acer ColorSafe II Technology, ColorBoost 3D Technology, Acer LumiSense, Acer BlueLight Shield

#### Lens

Zoom Factor	1.1x
Keystone Correction Direction	Vertical
Vertical Keystone Correction	-40 / +40

#### Video Input

TV System	NTSC, SECAM, PAL
Video Interfaces	VGA, HDMI, composite video

#### Speakers

Type	Integrated
Sound Output Mode	Mono
Output Power / Channel	3 Watt
Speakers	1 x mixed channel

#### Expansion / Connectivity

Interfaces	1 x HDMI - 19 pin HDMI Type A 1 x VGA input - 15 pin HD D-Sub (HD-15) 1 x USB - 4 pin USB Type A 1 x audio line-in 1 x composite video input - RCA 1 x VGA output 1 x audio line-out
------------	--

#### Miscellaneous

Included Accessories	Lens cover, remote control, battery for remote control, security card
Cables Included	1 x VGA cable

#### Power

Power Source	AC
Nominal Voltage	AC 120/230 V
Power Consumption Operational	275 Watt

## Dimensions &Weight

Width	31.3 cm
Depth	24 cm
Height	11.37 cm
Weight	2.7 kg

## Manufacturer Warranty

Service &Support	Limited warranty - 2 years Limited warranty - lamp - 1 year
------------------	--

## Environmental Parameters

Min Operating Temperature	0 °C
Max Operating Temperature	40 °C
Humidity Range Operating	80%

## What's in the box

Acer X138WHP  
Lens cover,remote control,battery for remote control,security card  
VGA cable

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet