

Acer C250i(MR.JRZ11.001)

Acer C250i - DLP projector - LED - 300 ANSI lumens - Full HD (1920 x 1080) - 1080p - Bluetooth



The Acer C250i is a Full HD portable LED projector designed to project smartphone content anywhere, anytime.

## Key Selling Points

High-quality Full HD resolution and wireless performance  
An abundance of connectivity options

## Product Features

High-quality Full HD resolution and wireless performance

Despite its compact size, the C250i supports beautiful high-definition imagery and a long battery. The C250i's LED module offers a long lifespan and high brightness. The projector's built-in Bluetooth speakers are rated at 5 watts for best-in-class sound when watching movies or TV shows.

An abundance of connectivity options

In addition to wireless connectivity, the Acer C250i also features a standard HDMI port for connecting and viewing content on a laptop or desktop computer. USB Type-C and Type-A ports support video-out for smartphones and PCs alike, and no additional software or drivers are needed. The USB Type-A port allows direct multimedia playback from a USB drive for an incredibly sleek and PC-free projection experience.

## Main Specifications

Product Description	Acer C250i - DLP projector - Bluetooth
Device Type	DLP projector - 1080p
Built-in Devices	microSD card reader
Localisation	EMEA
Brightness	300 ANSI lumens
Contrast Ratio	5000: 1
Resolution	Full HD (1920 x 1080)
Bulb type	LED
Bulb life cycle	Up to 30000 hour(s)
Video Input	Bluetooth
Speakers	Speaker(s) - internal
Dimensions (WxDxH)	18.6 cm x 10 cm x 10 cm
Weight	600 g

## Extended Specification

### General

Device Type	DLP projector - 1080p
Built-in Devices	microSD card reader
Localisation	EMEA

### Projector

Brightness	300 ANSI lumens
Contrast Ratio	5000: 1
Resolution	Full HD - Full HD (1920 x 1080)
Bulb type	LED
Bulb life cycle	Up to 30000 hour(s)
Features	360° projection,100% NTSC colour gamut,portrait projection,Acer TrueHarmony

#### Video Input

Video Interfaces	HDMI
LAN and Wireless Image Transferring Protocols	Bluetooth

#### Speakers

Type	Internal
Output Power / Channel	5 Watt

#### Expansion / Connectivity

Interfaces	1 x USB-C 1 x USB - 4 pin USB Type A 1 x headphones 1 x HDMI - 19 pin HDMI Type A
------------	--

#### Miscellaneous

Included Accessories	Carrying case,wireless remote control
----------------------	---------------------------------------

#### Battery

Run Time (Up To)	5 hour(s)
------------------	-----------

#### Dimensions &Weight

Width	18.6 cm
Depth	10 cm
Height	10 cm
Weight	600 g

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet