

PRODUCT-DETAILS

# PAFS28/BL/25M

## STD WGT FINE BLK NYL COND NC28 25M




---

### General Information

|                       |   |
|-----------------------|---|
| Extended Product Type | PAFS28/BL/25M   |
| Product ID            | 7TCA296000R2231   |
| EAN                   | 5020963002540   |
| Catalog Description   | STD WGT FINE BLK NYL COND NC28 25M  |
| Long Description      | Standard Weight Conduit, Nominal Conduit Size 28mm, NW Conduit Size 23, Fine Conduit Pitch, Outside Diameter 28.5mm, Inside Diameter 22.6mm, Static Bend Radius 50mm, Reel Length 25 Meters, Polyamide (Nylon) 6, Black |

---

### Ordering

|                       |               |
|-----------------------|---------------|
| EAN                   | 5020963002540 |
| Customs Tariff Number | 3926909990    |

---

### Dimensions

|                    |                     |
|--------------------|---------------------|
| Product Net Weight | 5.62 lb<br>2.549 kg |
|--------------------|---------------------|

---

### Container Information

|                       |                 |
|-----------------------|-----------------|
| Package Level 1 Units | 1 piece         |
| Package Level 1 Width | 37 in<br>940 mm |

|                                |                 |
|--------------------------------|-----------------|
| Package Level 1 Height         | 17 in<br>432 mm |
| Package Level 1 Depth / Length | 17 in<br>432 mm |
| Package Level 2 Units          | 1 piece         |
| Package Level 2 Width          | 37 in<br>940 mm |
| Package Level 2 Height         | 17 in<br>432 mm |
| Package Level 2 Depth / Length | 17 in<br>432 mm |
| Package Level 3 Units          | 1 piece         |
| Package Level 3 Width          | 37 in<br>940 mm |
| Package Level 3 Height         | 17 in<br>432 mm |
| Package Level 3 Depth / Length | 17 in<br>432 mm |

### Additional Information

|                     |  |
|---------------------|--|
| Application         | Indoors / Outdoors - Light Industrial, Buildings & Machinery |
| Brand / Label       | Adaptaflex   |
| Color               | Black  |
| Flexibility         | High   |
| Inside Diameter     | 22.6 mm  |
| Material            | Polyamide/Nylon 6  |
| Nominal Size        | 28 mm  |
| Number of Batteries | 0  |
| Outside Diameter    | 28.5 mm  |
| Product Name        | ADAPTAFLEX   |
| Product Type        | Standard Weight Conduit with Fine Pitch                      |
| Radius              | 50 mm  |
| Special Functions   | High Fatigue Life, Self Extinguishing, Halogen Free          |
| UPC                 | 786210147604   |

### Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | PAFS28/BL/25M   |
| Declaration of Conformity - CE    | 9AKK107492A9618 |
| Instructions and Manuals          | PAFS28/BL/25M   |

### Classifications

|                                    |                                    |
|------------------------------------|------------------------------------|
| ETIM 6                             | EC001175 - Corrugated plastic hose |
| ETIM 7                             | EC001175 - Corrugated plastic hose |
| UNSPSC                             | 39131706                           |
| WEEE Category                      | Product Not in WEEE Scope          |
| IDEA Granular Category Code (IGCC) | 5535 >> Electrical conduit         |

---

## Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

