

PRODUCT-DETAILS

# SAMHL32/10M

## 32MM GALV CORE ANTI MICRO COND 10M



### General Information

Extended Product Type	SAMHL32/10M
Product ID	7TCA296030R0445
EAN	5020963801549
Catalog Description	32MM GALV CORE ANTI MICRO COND 10M
Long Description	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 32 Millimeters / US Trade Size 1 Inch, Outside Diameter 33.1mm, Inside Diameter 26.7mm, Static Bend Radius 144mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 10 Meters, White

### Ordering

EAN	5020963801549
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	15.32 lb 6.948 kg
--------------------	----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

---

### Additional Information

Application	Suitable for indoor splash zone areas or food processing equipment
Brand / Label	Adaptaflex
Color	White
Flexibility	High
Inside Diameter	26.7 mm
Material	Galvanised Steel Core, String Packed and Thermoplastic Jacket
Nominal Size	32 mm
Number of Batteries	0
Outside Diameter	33.1 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Anti-Microbial Conduit
Radius	144 mm
UPC	786210213002

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SAMHL32/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SAMHL32/10M

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

