

PRODUCT-DETAILS

# LNSS/M16

## M16 STAINLESS LOCKNUT



Product image  
not available

### General Information

Extended Product Type	LNSS/M16
Product ID	7TCA296120R0061
EAN	5020963806513
Catalog Description	M16 STAINLESS LOCKNUT
Long Description	Locknut, Size M16, Stainless Steel

### Ordering

EAN	5020963806513
Customs Tariff Number	7307225000

### Dimensions

Product Net Weight	.007 lb 3.175 g
--------------------	--------------------

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.25 in 6 mm
Package Level 1 Height	1 in 25 mm

Package Level 1 Depth / Length	1 in 25 mm
Package Level 2 Units	10 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	5 in 127 mm

---

### Additional Information

Application	To Be Used with Fittings When Securing Into Knockouts
Brand / Label	Adaptaflex
Color	Metallic
Construction Material	316 Stainless Steel
Number of Batteries	0
Product Name	STAINLESS STEEL LOCKNUT
Product Type	Locknut with Metric Threads
Thread Size	M16
Thread Standard	Metric
UPC	786210311944

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	LNSS/M16
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	LNSS/M16

---

### Classifications

ETIM 6	EC000940 - Locknut for cable screw gland
ETIM 7	EC000940 - Locknut for cable screw gland
UNSPSC	31161716
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	2849 >> Locknuts

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available