

PRODUCT-DETAILS

# FLH0510

## LT-H FLEXIBLE CONDUIT 25MM 10M



### General Information

Extended Product Type	FLH0510
Product ID	7TCA297020R0144
EAN	5011949202962
Catalog Description	LT-H FLEXIBLE CONDUIT 25MM 10M
Long Description	Liquid Tight, High Temperature Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 26.4mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, Reel Length 10 Meters, Galvanised Steel Core, String Packing with Thermoplastic Rubber Covering, Black

### Ordering

EAN	5011949202962
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	13.24 lb 6.005 kg
--------------------	----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

### Additional Information

Application	Extreme Temperature Environments
Brand / Label	Kopex
Color	Black
Flexibility	High
Inside Diameter	21.0 mm
Material	Galvanized Steel Core with String Packing and Thermoplastic Rubber Coating
Nominal Size	3/4 in NC25
Number of Batteries	0
Outside Diameter	26.4 mm
Product Name	flex metal conduit
Product Type	Liquid Tight High Temperature Conduit
Radius	110 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210276632

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLH0510
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLH0510

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

