

ECI-63.40-B00-K4 -



Characteristics of the drive solution

Typ	Unit	Value
Order number	-	VM.ECI6340BK4
Weight	kg	1.15
Length	mm	138
Ambient temperature	-	0°C to +40°C
Protection	-	IP 54

Motor

Typ	Unit	Value
Type of motor	-	brushless EC motor, internal rotor
Motor designation	-	ECI-63.40-B00-K4
Voltage	V	24
Output speed	rpm	4000
Nominal power	W	251.0
Rated current	A	12.3
Torque	Ncm	59.9
Operating capacitor	-	no
weight of Motor	kg	1.15