

ECI-63.20-B00-K4 -



Characteristics of the drive solution

Typ	Unit	Value
Order number	-	VM.ECI6320BK4
Weight	kg	0.85
Length	mm	118
Ambient temperature	-	0°C to +40°C
Protection	-	IP 54

Motor

Typ	Unit	Value
Type of motor	-	brushless EC motor, internal rotor
Motor designation	-	ECI-63.20-B00-K4
Voltage	V	24
Output speed	rpm	4000
Nominal power	W	178.0
Rated current	A	8.5
Torque	Ncm	42.5
Operating capacitor	-	no
weight of Motor	kg	0.85