



Data sheet | Item number: 762-4102

Touch Panel 600; 14.5 cm (5.7"); 640 x 480 pixels; 2 x USB, 2 x ETHERNET;
Web Panel




www.wago.com/762-4102



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Item description

PIO1 hardware configuration

- 2 x ETHERNET port for connecting to field devices and the engineering tool
- 2 x USB port for optional connection of a USB stick, mouse or keyboard

Data

Technical Data

Display diagonal	14,5 cm (5.7 Inches)
Display	Resistive touchscreen
Display colors	262,000 colors
Graphics resolution	(640 x 480) px
Visualization	Webserver
ETHERNET protocols	DHCP DNS FTP FTPS HTTP HTTPS SSH
Communication	Web browser (HTML5)
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM [®] Cortex™ A9
Main memory (RAM)	2,048 MB
Internal memory (flash)	4096 MB
Memory card type	microSD (max. 2 GB); microSDHC (max. 32 GB)

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



Indicators	five LEDs
Controls	Resistive touch panel, two capacitive keys, proximity sensor
Supply voltage	SELV DC 24 V (18 ... 31,2 V); with reverse voltage protection

Connection data

Connection technology: communication/fieldbus	Web browser: 2 x RJ-45; 2 x USB 2.0 host (type A)
---	---

Geometrical Data

Width	172 mm / 6.772 inch
Height	163 mm / 6.417 inch
Depth	58 mm / 2.283 inch
Panel cutout (W x H)	(157 x 148) mm

Mechanical data

Weight	843 g
--------	-------

Environmental Requirements

Surrounding air temperature (operation)	0 ... 55 °C
Surrounding air temperature (storage)	-20 ... 80 °C
Protection type	IP65
Note on protection type	IP65 (front side); IP20 (rear side), per EN 60529
Relative humidity (without condensation)	90 %
Mounting type	Clamping elements (included) or VESA mount (4 x M4x8)

Commercial data

Packaging type	BOX
Country of origin	DE
GTIN	4055143839433
Customs tariff number	84714100000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Additional Approval Text	Certificate name
	KC National Radio Research Agency	Article 58-2, Clause 3	MSIP- REM-W43- WBP762


Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com


Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



Ship Approvals

Logo	Approval	Additional Approval Text	Certificate name
	DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAA00001FS

UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	E175199

Counterpart

Compatible products

assembling

	Item no.: 762-9001 eIDISPLAY7300T ; Clamping elements (4 pieces)	www.wago.com/762-9001
--	--	--

Downloads

Documentation

Manual			
WAGO Touch Panel 600 Standard Line	1.2.0 Apr 7, 2020	pdf 2.9 MB	Download
Bid Text			
762-4102 X81 - Datei	Feb 19, 2019	xml 5.3 kB	Download

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



762-4102
docx - Datei

Dec 21, 2018

docx
21.4 kB

Download

System Description

Touch Panel 600, system description

pdf
727.2 kB

Download

Runtime Software

Firmware

Firmware: 762-4102 Touch Panel 600; 14.5 cm (5.7"); 640 x 480 pixels; 2 x USB, 2 x ETHERNET; Web Panel

15
Dec 9, 2019

zip
150.6 MB

Download

Handling Instructions

Product family

Standard Line

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!