

**XLR Type PCB Mounting -
3 Pole Die Cast**



NC3MD-V NC3MD-H NC3FD-V NC3FD-H
H=30, W=26, D=26.7, Panel cut-out B

- Unified metal shell for male and female
- Insert premounted to PCB, shell to enclosure
- Front or rear mount
- RF protected
- Available with either plain screw fixing holes or tapped M3 thread

224187

	Mftrs. List No.	Order Code	Price Each
Plugs - Plain Fixing Holes			
Straight	NC3MDV	308-845 ●	
90°	NC3MDH	308-857 ●	
Sockets - Plain Fixing Holes			
Straight	NC3FDV	308-869 ●	
90°	NC3FDH	308-870 ●	
Plugs - M3 Thread Fixing Holes			
Straight	NC3MDM3V	439-058 ●	
90°	NC3MDM3H	439-060 ●	
Sockets - M3 Thread Fixing Holes			
Straight	NC3FDM3V	439-071 ●	
90°	NC3FDM3H	439-083 ●	
Fitting Tool	SD-1	269-803	