



fitted with

- connected load**
- power consumption**
- luminous flux**
- luminous efficacy**
- light distribution**
- light color**
- color rendering index (CRI)**
- glare-free**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- lamp cover**
- balance of articulation joints**
- weight (net)**
- mains lead**
- fastening**
- special features**


LED

- 22-26 V; DC
- approx. 5 W
- approx. 460 lm
- approx. 92 lm/W
- direct, wide-angled beam
- neutral white, approx. 5000 K
- > 70
- screen
- IP 67
- III
- switchable
- external
- aluminium, painted, black
- glass screen
- friction
- approx. 0.9 kg (2.0 lbs)
- approx. 3 m (9.8 ft); with free stranded wires screw-down flange
- Flood with 30° angle of radiation





illuminance

distance: 50 cm
Em: 2969 lx
Emax: 5298 lx
Emin: 1085 lx



luminous intensity



dimensions in mm