

## SNB Series NEMA Sheet Metal Box



### Ordering Information

Part Number	External Height (in)	External Width (in)	External Depth (in)
SNB-3730	9.84	7.87	5.91
SNB-3731	11.81	9.84	5.91
SNB-3732	11.81	9.84	7.87
SNB-3733	11.81	11.81	5.91
SNB-3734	11.81	11.81	7.87
SNB-3735	15.75	11.81	5.91
SNB-3736	15.75	11.81	7.87
SNB-3737	15.75	15.75	7.87
SNB-3738	7.87	5.91	5.91
SNB-3739	7.87	7.87	3.98
SNB-3740	9.84	9.84	5.91
SNB-3741	9.84	7.87	3.98
SNB-3742	11.81	9.84	7.87
SNB-3743	15.75	13.98	7.87

*Priced, sold and packaged in quantities of one  
Contact the factory for modifications*

**BUD SNB Steel NEMA**

## Benefits and Features

- Designed to meet NEMA 1, 2, 4, 4x, 12, 13 and IP65 ratings
- UL listed and tested to UL508-4X requirements
- Continuous seam welded 16 ga. steel construction
- Cover closes securely with unique key provided
- Wall mounting holes located inside for security
- Bonding studs for grounding are provided on base and door
- Finish: smooth gray powder coat
- Easily machined and modified to your particular requirements

## Accessories

- Includes 14 ga. steel, zinc plated removable inner panel.

## Applications

- Instrument cases
- Control housings
- Terminal wiring enclosures

## Competition

- Meter cases
- Junction boxes
- Marine applications
- Wet and dirty industrial application
- Wash down environments

## Related Products

- Switches
- Pushbuttons
- Connectors
- Cable Glands

## Key Customer Contacts


- Design Engineers and Designers
- Manufacturing Engineers
- Electronic Engineers and Designers

## Questions to Ask

- Who specifies your enclosures?
- Do you need the durability of a steel enclosure?

## Availability

*In Stock*



Bud Industries, Inc.

4605 E. 355th Street  
Willoughby, Ohio 44094

[saleseast@budind.com](mailto:saleseast@budind.com)  
[saleswest@budind.com](mailto:saleswest@budind.com)

[www.budind.com](http://www.budind.com)

**BUD SNB Steel NEMA**