



24-Inch Bubble Level



Klein Tools' 24-Inch Bubble Level features powerful rare earth magnets with patented magnet track on one side and V-groove on the other. This precision machined level is accurate and durable with an orange body for visibility so it won't get lost on conduit or pipe. Rubberized end-caps provide increased drop protection of 9.9-Foot.

Specifications

Type:	Bubble with Adjustable Vial	Application:	Check for and find the true vertical and horizontal; Transfer angles between surfaces with adjustable vial
Special Features:	Rare Earth Magnets, Adjustable Bubble Vial, V-Groove on Top	Material:	Aluminum
Accuracy:	+/- 0.029°	Number of Vials:	3
Type of Vials:	0°, 90°, Adjustable	Top Read:	Yes
Vial Material:	Plastic	Magnet Type:	Rare Earth
Drop Protection:	9.9' (3 m)	Case Included:	No
Overall Length:	24" (61 cm)	Overall Height:	2.5" (6.4 cm)
Overall Width:	1" (2.5 cm)	Weight:	1.9125 lb (0.87kg)