

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200700237](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Bulkhead Feed-Through Receptacle, 5 Poles, Male (Straight) to Female (Straight)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120070
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Bulkhead Feed-Through
UPC	78678845499

Physical

Coupling Type	Internal Thread
Gender	Female-Male
Keyway	Single
Length	0.047m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M12 x 1.0
Net Weight	45.250/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Material Info

Engineering Number	8R5L30
--------------------	--------

Reference - Drawing Numbers

Sales Drawing	SD-120070-018
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120070 Series](#)