

DYMO®



LabelWriter™ Wireless

HIGH-SPEED LABEL PRINTER WITH WI-FI® CONNECTIVITY

- Save time - print up to 71 labels per minute*
- Thermal print technology - no ink or toner needed
- Built in Wifi for cable free printing
- Add a single LabelWriter™ Wireless to a network and bring label printing to everyone
- Free DYMO Label Software allows for quick design and printing of labels from a MAC® or PC, or use Microsoft® Office plugins to print directly from Microsoft® Word, Excel® or Outlook®
- For even more features, download DYMO Connect



Single Unit Includes:

- LabelWriter® Wireless
- Address Labels Starter Roll - 36x 89mm
- Charging Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty**



LabelWriter Wireless Quick Specs	
Unit Dimensions (H x W x L)	124 x 127 x 204 mm
Weight (excluding labels/spool)	633 g
Mac®/PC Compatible	Yes via DYMO Connect
Mobile Compatibility	Yes via DYMO Connect
Max Label Width	62 mm
Tape Platform	LW
Resolution	600 x 300 dpi
Printing System	Direct Thermal
Print Speed	71 labels/minute*
Barcodes	Yes
Power Source	Adapter Power Cable
Networking	Yes – Wi-Fi® 802.11b/g/n
Interface	USB, Wi-Fi®
Country of Origin	China

* 4-line address label

Item Number	Description	Unit	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
2000932	LabelWriter Wireless	Unit	25.4	17.4	18.4	1	3501170009321	
Accessories (www.dymo.com)								
2025674	Wireless Power Adapter	Unit	13.4	24.4	6.1	1	0071701060648	
2025675	Power Cable	Unit	13.4	24.4	6.1	1	3026980256753	
1997364	Micro USB Cable	Unit	13.4	24.4	6.1	1	0001179003502	
2025672	Spool	Unit	13.4	24.4	12.0	1	0071701060655	
60622	LabelWriter Cleaning Card 10pack	Unit	9.02	12.7	3.05	1	0097043606221	

** +1 year if registered on the Dymo website

LW Standard labels

Hassle-free labels for all your mailing, shipping and organizational needs.

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	130	2	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	130	24	Permanent	Paper
	Standard Address Labels	2093091	28 x 89	130	12	Permanent	Paper
	Assorted Colour labels	S0722380	28 x 89	130	4	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	260	2	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	260	24	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	260	1	Permanent	Transparent Plastic
	Large Return Address Label	S0722520	25 x 54	500	1	Permanent	Paper
Shipping	Shipping / Name badge Labels	S0722430	54 x 101	220	1	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	575	2	Permanent	Paper
	Shipping / Name badge Labels	2093092	54 x 101	220	6	Permanent	Paper
	Shipping / Name badge Labels	S0722420	54 x 101	220	12	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	220	1	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1000	1	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	750	1	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	500	1	Removable	Paper
	Multi-Purpose Labels	S0722540	32 x 57	1000	1	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	320	1	Permanent	Paper
	Large Multi-Purpose Labels	2093094	32 x 57	1000	6	Permanent	Paper
	Large Multi-Purpose Labels	2093095	32 x 57	1000	12	Permanent	Paper
Specialty	Suspension file labels	S0722460	12 x 50	220	1	Permanent	Paper
	LAF Labels small	S0722470	38 x 190	110	1	Permanent	Paper
	LAF Labels large	S0722480	59 x 190	110	1	Permanent	Paper
	Small name badge label	S0722560	41 x 89	300	1	Removable	Paper
	Appointment / name badge cards	S0929100	51 x 89	300	1	Non-adhesive	Paper

LW Durable Labels

Tear-resistant, coated polypropylene labels with extra-strength adhesive that withstand abrasion, common cleaners, and a wide range of temperatures-ideal for shelving, storage, and signage.



Water



Solvents



Oil



Textured Surfaces



Temperature
-18°C to 50°C

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Durable	LW Durable Labels	1933081	25 x 89	350	1	Permanent	Coated Polypropylene
	LW Durable Labels	1976411	25 x 54	160	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933088	59 x 102	300	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933085	19 x 64	450	2	Permanent	Coated Polypropylene
	LW Durable Labels	1933083	25 x 25	850	2	Permanent	Coated Polypropylene
	LW Durable Labels	1933084	57 x 32	800	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933087	59 x 190	170	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933086	104 x 159	200	1	Permanent	Coated Polypropylene

The DYMO high quality labels are made in Belgium