

# Most Ruggedized Industrial Displays - FPM

## Harsh Environment

Front panel IP66 protection  
Wide temp support (-20~60C)  
Higher EMC (Ind.: CS10, consumer: CS3) ⚡  
50~70K HRs backlight lifetime  
DC Power Input



## Stainless Steel Enclosure

Chemicals/ detergent resistant  
wildly deployed in Pharma, F&B industries



## C1D2 Certified

ruggedized monitors in hazardous area



# Two Steps to Pick the Model You Need

1. Monitor size and ratio (4:3/16:9)
2. Ruggedized features for vertical (i.e. Wide temp, stainless steel, C1D2 certified)

P/N	Description	Size	Touch	Video Input	True Flat	Wide Temp	Power	List Price
<b>Widescreen Monitor with Multi-touch</b>								
FPM-7151W-P3AE	15.6" Wide Screen Ind. Monitor w/PCT TS (VGA/DVI)	15.6	PCAP	VGA/DVI	V	-	DC	\$1086
FPM-7181W-P3AE	18.5" Wide Screen Ind. Monitor w/PCT TS (VGA/DVI)	18.5	PCAP	VGA/DVI	V	-	DC	\$1212
FPM-7211W-P3AE	21.5" Wide Screen Ind. Monitor w/PCT TS (VGA/DVI)	21.5	PCAP	VGA/DVI	V	-	DC	\$1339
FPM-215W-P4AE	15.6" Wide Screen Ind. Monitor w/ PCAP TS (HDMI)	15.6	PCAP	HDMI	V	-	AC/DC ADP	\$820
FPM-221W-P4AE	21.5" Wide Screen Ind. Monitor w/ PCAP TS (HDMI)	21.5	PCAP	HDMI	V	-	AC/DC ADP	\$960
<b>4:3 True-flat Wide Temp Monitor</b>								
FPM-7061T-R3AE	6.5" VGA Ind Monitor w/RS TS (VGA/DP), Wide Temp	6.5	RS	VGA/DP	V	V	DC	\$561
FPM-7121T-R3AE	12.1" XGA Ind Monitor w/RS TS (VGA/DP), Wide Temp	12.1	RS	VGA/DP	V	V	DC	\$798
FPM-7151T-R3AE	15" XGA Ind Monitor w/RS TS (VGA/DP), Wide Temp	15	RS	VGA/DP	V	V	DC	\$855
FPM7121TR3A1701E-T	(Sunlight Readable) 12.1" Ind Monitor w/Resistive TS (VGA/DP), Wide Temp, UV	12.1	RS	VGA/DP	V	V	DC	\$1182
FPM7151TR3A1602E-T	(Sunlight Readable) 15" Ind Monitor w/Resistive TS (VGA/DP), Wide Temp, UV	15	RS	VGA/DP	V	V	DC	\$1582
<b>4:3 Stainless Steel Wide Temp Monitor</b>								
FPM-8151H-R3BE	15" <b>C1D2-certified</b> Stainless Steel Ind. Monitor w/RS TS (VGA/DVI), Wide Temp	15	RS	VGA/DVI	-	V	DC	\$1637
FPM-815S-R6AE	15" Stainless Steel Ind. Monitor w/ RS TS (VGA/DP), Wide Temp	15	RS	VGA/DP	V	V	DC	\$855
FPM-817S-R6AE	17" Stainless Steel Ind. Monitor w/ RS TS (VGA/DP), Wide Temp	17	RS	VGA/DP	V	V	DC	\$885