




## Dimensions

DIN 965  
BS 4183  
ISO 7046

Materials / Finishes:  
Steel 4.8 / Zinc & clear  
Other materials and finishes available on request



d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
H max (BS / DIN)	1.2	1.5	1.65	1.93	2.2	2.5	3	4.5
H max (ISO)	1.2	1.6	1.65	2.35	2.7	2.7	3.3	4.65
recess (BS / DIN)	1	1	1	2	2	2	3	4
recess (ISO)	0	1	1	2	2	2	3	4
D nom (BS)	-	5.5	6.3	7.35	8.4	10	12	16
D nom (DIN)	3.8	4.7	5.6	6.5	7.5	9.2	11	14.5
D nom (ISO)	3.8	4.7	5.5	7.3	8.4	9.3	11.3	15.8

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

## Preferred sizes - Steel

d	M2	M2.5	M3	M3.5	M4	M5	M6	M8
L	4	<b>TR</b>						
	5	<b>TR</b>						
	6	<b>TR</b>	<b>TR</b>		<b>TR</b>			
	8	<b>TR</b>	<b>TR</b>		<b>TR</b>			
	10	<b>TR</b>	<b>TR</b>		<b>TR</b>	<b>TR</b>		
	12	<b>TR</b>	<b>TR</b>		<b>TR</b>	<b>TR</b>	<b>TR</b>	
	16	<b>TR</b>	<b>TR</b>		<b>TR</b>	<b>TR</b>	<b>TR</b>	
	20			<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>
	25			<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>
	30			<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>
	35			<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>
	40				<b>TR</b>	<b>TR</b>	<b>TR</b>	<b>TR</b>
	45					<b>TR</b>	<b>TR</b>	<b>TR</b>
	50					<b>TR</b>	<b>TR</b>	<b>TR</b>
60								