


KF-P STRAIGHT CONNECTORS FOR STANDARD AND MEDIUM DUTY FLEXIBLE NON-METALLIC CONDUITS



SUITABLE FOR USE WITH FINE PITCH (T) CONDUITS

MATERIAL: NYLON 6, HALOGEN FREE.

CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIAMETER	MINIMUM BORE	ACROSS FLATS	THREAD LENGTH	NOMINAL LENGTH
12	Metric to BS6053	12mm	YQM* 0202	12.0	7.8	25.0	12.0	34.9
16		16mm	YQM* 0303	16.0	11.5	25.8	12.0	34.9
16		20mm	YQM* 0304	20.0	15.0	25.8	12.0	34.9
20		20mm	YQM* 0404	20.0	15.0	30.8	12.0	34.9
25		25mm	YQM* 0505	25.0	20.6	38.6	12.0	36.9
32		32mm	YQM* 0606	32.0	27.0	48.0	12.0	36.9
10	Pg to DIN 40430	Pg7	YQP* 0101	12.5	6.8	22.0	12.0	24.9
12		Pg9	YQP* 0202	15.2	7.8	25.0	12.0	34.9
16		Pg11	YQP* 0303	18.6	11.5	25.8	12.0	34.9
20		Pg13.5	YQP* 0404	20.4	15.0	30.8	12.0	34.9
20		Pg16	YQP* 0405	22.5	16.0	30.8	12.0	34.9
25		Pg21	YQP* 0506	28.3	22.3	38.6	12.0	36.9
32		Pg29	YQP* 0607	37.0	27.0	48.0	12.0	36.9

SUITABLE FOR USE WITH COARSE PITCH (G) CONDUITS

CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIAMETER	MINIMUM BORE	ACROSS FLATS	THREAD LENGTH	NOMINAL LENGTH
20	Metric to BS6053	20mm	YVM* 0404	20.0	14.75	33.0	12.0	34.9
25		25mm	YVM* 0505	25.0	20.35	41.0	12.0	36.9
32		32mm	YVM* 0606	32.0	26.75	48.0	12.0	36.9
25	Pg to DIN40430	Pg21	YVPB 0506	28.3	20.35	41.0	12.0	36.9
32		Pg29	YVPB 0607	37.0	26.75	48.0	12.0	36.9
40		Pg36	YVP* 0708	47.0	34.75	56.0	12.0	44.0
50		Pg48	YVP* 0810	59.3	45.75	68.0	12.0	44.0

* ADD 'B' FOR BLACK

PROPERTIES:

IP RATING WITH RECOMMENDED CONDUITS

OPERATING TEMPERATURE APPROVALS

IP 66 (NO INGRESS OF TALCUM POWDER UNDER VACUUM AND NO INGRESS OF WATER WITH NOZZLE SPRAY FROM 3m).

- 40° C TO 120° C

UR COMPONENT RECOGNISED.

FITTINGS INSTRUCTIONS INCLUDED WITH PRODUCT AND AVAILABLE ON REQUEST – LEAFLET No.808898

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.