

18v LXT Combi Drill

DHP482RTWJ

Model DHP482 is a cordless hammer driver drill that has been developed as the successor to the current model DHP456.



TECHNICAL SPECIFICATIONS

Capacity in Steel	13 mm
Capacity in Wood	38 mm
Chuck Capacity	1.5 - 13 mm
No Load Speed (Hi)	0 - 1,900 rpm
No Load Speed (Lo)	0 - 600 rpm
Blows per Minute (Hi) - ipm	0 - 28,500 ipm
Blows per Minute (Lo) - ipm	0 - 9,000 ipm
Capacity in Masonry	13 mm
Voltage	18 v
Torque Settings	21 + drill
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec ²
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Net weight	1.5 - 1.8 kg
Battery quantity (4.0Ah)	0
Battery Quantity (5.0ah)	2

USER BENEFITS

- Electric brake
- 2 mechanical gears.
- Variable speed control by trigger
- Forward / reverse rotation
- Twin LED job light
- Ergonomic soft grip
- Keyless Chuck
- Compact and lightweight design
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Metal gears

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

STANDARD ACCESSORIES

197282-4

Battery BL1850B 18v Li-ion



821550-0

MAKPAC CONNECTOR CASE (TYPE



837916-4

MAKPAC INLAY FOT TYPE 2 CASE



DC18RC

DC18RC COMPACT CHARGER



OTHER