

## HSS Twist Black Oxide Drill Bits



### Specifications

Material : HSS4341  
 Standard : DIN338  
 Angle : 118 Degree

## HSS Twist Titanium Drill Bits



### Specifications

Material : HSS4341  
 Standard : DIN338  
 Angle : 118 Degree

## HSS Twist Cobalt Drill Bits



### Specifications

Material : M35 with 5% cobalt  
 Standard : DIN338  
 Angle : 135 Degree

## Part Number Table

Description	Drill Bit Size		Effective Length	Overall Length	Part Number
	Metric	Imperial			
HSS Twist - Black Oxide	3.5mm	9/64"	39mm	70mm	MP004487
	4mm	5/32"	43mm	75mm	MP004488
	4.2mm	11/64"	43mm	75mm	MP004489
	6.5mm	1/4"	63mm	101mm	MP004490
	6.8mm	17/64"	69mm	109mm	MP004491
	7.5mm	19/64"	69mm	109mm	MP004492
	8mm	5/16"	75mm	117mm	MP004493
	8.5mm	21/64"	75mm	117mm	MP004494
	9mm	11/32"	81mm	125mm	MP004495
9.5mm	3/8"	81mm	125mm	MP004496	

# HSS Twist Drill Bits

Description	Drill Bit Size		Effective Length	Overall Length	Part Number
	Metric	Imperial			
HSS Twist - Titanium	1mm	1/32"	12mm	34mm	MP004497
	1.5mm	1/16"	18mm	40mm	MP004498
	2mm	5/64"	24mm	49mm	MP004499
	2.5mm	3/32"	30mm	57mm	MP004500
	3mm	7/64"	33mm	61mm	MP004501
	3.2mm	1/8"	36mm	65mm	MP004502
	3.5mm	9/64"	39mm	70mm	MP004503
	4mm	5/32"	43mm	75mm	MP004504
	4.2mm	11/64"	43mm	75mm	MP004505
	4.5mm	3/16"	47mm	80mm	MP004506
	5mm	13/64"	52mm	86mm	MP004507
	5.5mm	7/32"	57mm	93mm	MP004508
	6mm	15/64"	57mm	93mm	MP004509
	6.5mm	1/4"	63mm	101mm	MP004510
	6.8mm	17/64"	69mm	109mm	MP004511
	7mm	9/32"	69mm	109mm	MP004512
	7.5mm	19/64"	69mm	109mm	MP004513
	8mm	5/16"	75mm	117mm	MP004514
	8.5mm	21/64"	75mm	117mm	MP004515
	HSS Twist - Cobalt	9mm	11/32"	81mm	125mm
9.5mm		3/8"	81mm	125mm	MP004517
10mm		25/64"	87mm	133mm	MP004518
1mm		1/32"	12mm	34mm	MP004519
1.5mm		1/16"	18mm	40mm	MP004520
2mm		5/64"	24mm	49mm	MP004521
2.5mm		3/32"	30mm	57mm	MP004522
3mm		7/64"	33mm	61mm	MP004523
3.2mm		1/8"	36mm	65mm	MP004524
3.5mm		9/64"	39mm	70mm	MP004525
4mm		5/32"	43mm	75mm	MP004526
4.2mm		11/64"	43mm	75mm	MP004527
4.5mm		3/16"	47mm	80mm	MP004528
5mm	13/64"	52mm	86mm	MP004529	
5.5mm	7/32"	57mm	93mm	MP004530	
6mm	15/64"	57mm	93mm	MP004531	
6.5mm	1/4"	63mm	101mm	MP004532	

# HSS Twist Drill Bits

Description	Drill Bit Size		Effective Length	Overall Length	Part Number
	Metric	Imperial			
HSS Twist - Cobalt	6.8mm	17/64"	69mm	109mm	MP004533
	7mm	9/32"	69mm	109mm	MP004534
	7.5mm	19/64"	69mm	109mm	MP004535
	8mm	5/16"	75mm	117mm	MP004536
	8.5mm	21/64"	75mm	117mm	MP004537
	9mm	11/32"	81mm	125mm	MP004538
	9.5mm	3/8"	81mm	125mm	MP004539
	10mm	25/64"	87mm	133mm	MP004540

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.