



#23465

## USB 4-in-1 streaming microphone

Premium streaming microphone with 4 recording patterns to get the best performance in any situation

### Key features

- Digital USB connection; instantly works on any PC and laptop
- 4 recording patterns: cardioid, bidirectional, stereo and omnidirectional for optimised audio recordings in any situation
- Zero-latency headphone monitoring port, to listen to what you're recording in real-time, without delay
- Warm, rich and clear audio reproduction; for capturing vocals as well as acoustic instruments
- Perfect for podcasts, vlogs, voice-overs, music recording or streaming on YouTube, Twitch and Facebook
- Convenient microphone gain, mute & headphone volume knobs on the front of the microphone



### What's in the box

- Microphone with tripod stand
- USB-C to USB-A cable
- User guide
- Gaming sticker

### System requirements

- PC or laptop with USB port
- Windows 7, 8, 10 or Mac OS X 10.5 (Leopard) or higher
- Or
- PS4™



5 COLOURS  
■ ■ ■ ■ ■

4

RECORDING  
MODES



PERFECT FOR  
STREAMING



MUTE  
MICROPHONE



## Take Your Recordings to the Next Level

Whether you're looking for a microphone to record your podcast or music track, or to stream a gaming session, the Trust GXT 258 Fyru 4-in-1 Streaming Microphone takes your recordings to the next level. Meet the multi-purpose mic that features excellent audio quality whilst being extremely easy to use.

## Excellent Audio Quality

Of all things, the microphone you use has the biggest effect on your recordings. It has to capture voices and instruments in the highest possible quality. That's why the Trust GXT 258 Fyru 4-in-1 Streaming Microphone is built to deliver crystal clear and rich recordings of a near-professional studio quality.



## Record Your Way: 4 Different Patterns

The Fyru allows for recording in 4 different ways, optimised for any situation. Use cardioid if you want to get a clear recording without background noises – ideal for one-person podcasts. Opt for bidirectional if you're recording a duet or conducting an interview. Stereo is the go-to pattern to record a stereo music setting, or you can capture all surrounding sounds with the omnidirectional pattern, perfect if you're hosting a group-podcast.

## Easy Setup for Any Purpose

Amazingly easy to use, the Trust GXT 258 Fyru 4-in-1 Streaming Microphone comes with a plug-and-play USB connection to instantly connect to your PC or laptop. Its ease of use makes this microphone the ideal gadget for various purposes; from podcast, vlog, voice-over and music recording to games streaming on YouTube, Twitch and Facebook.





## Heavy Metal Design with LED Lights

The Fyru comes in a durable metal design with a metal grille front. Use the universal 5/8" screw mount to attach the Fyru to any compatible microphone arm or mount it to the tripod stand, guaranteeing optimal stability. Furthermore, the microphone is enhanced with adjustable LED lighting in 5 colours, to lighten up your recordings.

## Extra Pro Features

To perfect your recordings, you can listen to them in real-time, with the Fyru's zero-latency headphone monitoring port. Furthermore, you can regulate your settings with convenient microphone gain, mute and headphone volume knobs on the front of the microphone. And the internal pop filter filters out plosives and fricatives (unwanted sounds from letters like P and F) for even smoother recordings.



**GENERAL**

<b>Application</b>	Desktop, Home, Indoor	<b>Height of main product (in mm)</b>	183 mm
<b>Width of main product (in mm)</b>	63 mm	<b>Depth of main product (in mm)</b>	74 mm
<b>Total weight</b>	1030 g	<b>Weight of main unit</b>	626 g

**CONNECTIVITY**

<b>Connection type</b>	Wired	<b>Connector type</b>	USB
<b>Cable length main cable</b>	180 cm		

**MICROPHONE**

<b>Sensor type microphone</b>	Condenser	<b>Pick-up pattern</b>	Bidirectional, Cardioid, Omnidirectional, Stereo
<b>Sampling rate</b>	16bit, 48kHz	<b>Signal-to-noise ratio</b>	130 dB
<b>Noise reduction</b>	False	<b>Echo cancellation</b>	False

**MOUNT**

<b>Type of stand</b>	Tripod
----------------------	--------

**AUDIO**

<b>Frequency response</b>	30 - 18000 Hz
---------------------------	---------------

**HEADPHONE**

<b>Impedance</b>	32 Ohm	<b>Sensitivity</b>	-36 dB
------------------	--------	--------------------	--------

**CONTROL**


<b>Controls</b>	Lights on/off, microphone mute, volume control
-----------------	--

**COMPATIBILITY**


<b>Compatible Device Types</b>	Gaming console, laptop, pc	<b>Compatible Consoles</b>	PS4
<b>Compatible Software Platforms</b>	Mac OS, Windows		



**PRODUCT VISUAL 1**



**PRODUCT PICTORIAL 1**



**PRODUCT PICTORIAL 2**



**PRODUCT PICTORIAL 3**



**PRODUCT PICTORIAL 4**



**PRODUCT PICTORIAL 5**



**LIFESTYLE VISUAL 1**



**LIFESTYLE VISUAL 2**



**PRODUCT VISUAL 2**



**PRODUCT SIDE 1**



**PRODUCT FRONT 1**



**PRODUCT FRONT 2**