

Datasheet

**IEC Bolt Thermocouple with 2m of Glass Fibre Stainless Steel Over Braided Cable**



Bolt sensors is generally screwed into the surface which normally increases the speed of response and sensitivity of the measurement. Suitable for use up to +250°C.

- Available in type 'K' or 'J'
- Bolts have grounded junctions
- Bolt thread/pitch sizes available: M8 x 1mm  
M10 x 1mm  
M12 x 1mm
- Bolt lengths available 13 or 25mm
- Each bolt has 2 metres of glass fibre stainless steel over braided cable, terminating in bare tails
- Suitable for use up to +250°C

Type	Thread Pitch	Thread Length	Cable Length	Order Code
J	M8 x 1mm	13mm	2m	<b>XF-1424-FAR</b>
J	M8 x 1mm	25mm	2m	<b>XF-1425-FAR</b>
J	M10 x 1mm	13mm	2m	<b>XF-1426-FAR</b>
J	M10 x 1mm	25mm	2m	<b>XF-1427-FAR</b>
J	M12 x 1mm	13mm	2m	<b>XF-1428-FAR</b>
J	M12 x 1mm	25mm	2m	<b>XF-1429-FAR</b>
K	M8 x 1mm	13mm	2m	<b>XF-1430-FAR</b>
K	M10 x 1mm	13mm	2m	<b>XF-1431-FAR</b>
K	M10 x 1mm	25mm	2m	<b>XF-1432-FAR</b>
K	M12 x 1mm	13mm	2m	<b>XF-1433-FAR</b>
K	M12 x 1mm	25mm	2m	<b>XF-1434-FAR</b>