



MEACO  
PLATINUM  
RANGE

MEACO 25L LOW ENERGY

# Dehumidryer

*The real low cost alternative to the tumble dryer*



***'A breakthrough in dehumidifier design, the harder it works the less energy it uses. Combine this with the super high airflow and you have a real alternative to a tumble dryer'***



# MEACO 25L LOW ENERGY DEHUMIDRYER



The Meaco 25L Low Energy Dehumidryer has been designed to dry your clothes and it can do so faster and cheaper than any other dehumidifier thanks to its ground breaking DC Motor, large extraction rate, high air flow and energy efficient compressor.

For the first time ever you now have a viable option to a tumble dryer and if are worried about the cost of running a tumble dryer or do not have space for a tumble dryer then the Meaco 25L Low Energy Dehumidryer is the sensible alternative.

Leaving clothes to dry naturally indoors during winter will result in high levels of moisture in your home which will make your house feel colder, the air more expensive to heat and could result in mould growth and condensation.

At just 270 watts running costs this dehumidifier extracts water cheaper than any other 25 litre on the market and the beauty of a DC Motor is that the harder you work the dehumidifier the less energy it uses.

As well as being great at drying laundry the 25L makes a sensible choice for anyone needing a dehumidifier for a larger home or a storage space. There are four modes to choose from;

- Humidistat Mode** choose your target relative humidity between 30 and 80%rh
- Laundry Mode** makes use of the 280m<sup>3</sup>/hour fan to speed dry your clothes
- Quiet mode** reduces the fan speed to low and turns off the bleeper
- Auto mode** regulates the compressor and fan speed depending on the room humidity to maintain a comfortable environment

As well as the above the 25L features a child lock, an ioniser to help clean the air and auto-restart to remember it's settings after a power cut.

Part of the exclusive Meaco Platinum Range the Meaco 25L Low Energy Dehumidryer is the most energy efficient compressor dehumidifier in the award winning Meaco range.



## SPECIFICATIONS

Drying Capacity (Litres/24 Hours)	26.7°C - 60%rh	13.6L in Laundry Mode
	30.0°C - 80%rh	26.4L in Laundry Mode
Power Consumption (Watts)	26.7°C - 60%rh	270W
	30.0°C - 80%rh	330W
Air Flow (m <sup>3</sup> /hr)	150/170/215/280	
Modes	Humidistat Mode	
	Laundry Mode	
	Quiet Mode	
	Auto Mode	
Meaco Control Logic	Yes	
Auto restart	Yes	
Ioniser	Yes	
Child lock	Yes	
Off Timer	1-12 hours	
Tank Size	5 litres	
Temperature Range	+5°C/+35°C	
Relative Humidity Range	30% - 90%rh	
Refrigerant	R134a/195g	
Dehumidifier Dimensions (mm - w x d x h)	378 x 287 x 644	
Nett/Gross Weight (Kgs)	15.0/16.4Kgs	

## APPLICATIONS



Condensation



Mould



Damp



Laundry drying



Bathroom



Kitchen



Flats to 5 bedroom houses



Low running costs