



CR1306

13A SP SWITCHED SOCKET DUAL EARTH

BS 1363-2

2 GANG
CR1306


Switched Socket

Dimension

Height	86mm
Width	146mm
Plate Depth	9mm
Overall Depth (including rocker)	29mm

Back Box

Surface Moulded	9048
Flush Galvanised	SB665
Dry Lining	SB629



CR1306/D

CR1305/D

13A DP SWITCHED SOCKET DUAL EARTH

BS 1363-2

2 GANG
CR1306/D
CR1305/D


Switched Socket
Complete with LED

Dimension

Height	86mm
Width	146mm
Plate Depth	9mm
Overall Depth (including rocker)	29mm

Back Box

Surface Moulded	9048
Flush Galvanised	SB665
Dry Lining	SB629



CR1306/USB/D

CR1306/RCD

13A DP SWITCHED SOCKET DUAL EARTH WITH DUAL USB OUTLETS

BS 1363-2:2016, BS EN 60950-1

2 GANG
CR1306/USB/D 2.1A Shared USB Output

13A DP SRCD SWITCHED SOCKET

BS 1363-2, BS 7288, BS 5733, IPC-A-610, IEC62640

2 GANG
CR1306/RCD Switched Passive Socket
30mA RCD Protected

Dimension

Height	86mm
Width	146mm
Plate Depth	USB 9mm SRCD 14.85mm
Overall Depth (including rocker)	USB 37.5mm SRCD 45mm

Back Box

Surface Moulded	9040
Flush Galvanised	SB625
Dry Lining	SB629

