

IP20 LED Batten - Twin

LED IP20 BATTEN L1800 TWIN 4000K

0045165

Product features

- full range of LED Battens to replace traditional T8 battens (600mm, 1200mm, 1500mm and 1800mm), ease of installation, 4000K, 25000h lifetime



PRODUCT OVERVIEW

IPC Code	0045165
Product name	LED IP20 BATTEN L1800 TWIN 4000K
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000109
Fixture luminous flux (lm)	5600
Luminaire efficacy (lm/W)	117
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Photobiological Risk Group	RG0
Total power consumption (W)	48
Electrical protection	Class I
IP rating	IP20
IK rating	IK02
Product EAN number	5410288451657
Lamps	No

DATA TABLE

General data

IPC Code	0045165
Product name	LED IP20 BATTEN L1800 TWIN 4000K
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000109

Optical data

Fixture luminous flux (lm)	5600
Luminaire efficacy (lm/W)	117
Colour temperature (K)	4000
Light colour	Neutral White

IP20 LED Batten - Twin

LED IP20 BATTEN L1800 TWIN 4000K
0045165

CRI (Ra)	80
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	48
Mains voltage (V)	220-240V~
Electrical protection	Class I
Drive current (mA)	115
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	21
Max. Luminaires per 13A C Breaker	27
Max. Luminaires per 16A C Breaker	33
Max. Luminaires per 20A C Breaker	42
Max. Luminaires per 10A B Breaker	14
Max. Luminaires per 13A B Breaker	18
Max. Luminaires per 16A B Breaker	22
Max. Luminaires per 20A B Breaker	28

Lifetime data

Lumen maintenance - L70 B50	25000
-----------------------------	-------

Physical data


IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	1800
Nominal Product Width (mm)	82
Nominal Product Height (mm)	48
Weight (kg)	1.3

Packaging

Single packaging type	Mix blister(20% carton, 80% pl)
Product EAN number	5410288451657
Packaging single length / height (cm)	181.0
Packaging single width (cm)	8.6
Packaging single depth (cm)	5.2
DUN14 (outer)	15410288451654
Units per outer package	8
Packaging outer length / height (cm)	182.5
Packaging outer width (cm)	45.5
Packaging outer depth (cm)	23.5

PHOTOMETRY


IP20 LED Batten - Twin LED IP20 BATTEN L1800 TWIN 4000K 0045165



0.5	2.03	E(0°) E(C0)	63.8°	5970 257
1.0	4.06	E(0°) E(C0)	63.8°	1490 54
1.5	6.10	E(0°) E(C0)	63.8°	653 29
2.0	8.13	E(0°) E(C0)	63.8°	373 16
2.5	10.16	E(0°) E(C0)	63.8°	239 10
3.0	12.19	E(0°) E(C0)	63.8°	166 7

Distance [m] Cone diameter [m] Illuminance [lx]
C0 - C180 (Half beam angle: 127.6°)

TECHNICAL DRAWINGS



SYLVANIA 0045165


This luminaire contains built-in LED lamps

LED

The lamps cannot be changed in the luminaire.



874/2012

IP20 LED Batten - Twin *LED IP20 BATTEN L 1800 TWIN 4000K* 0045165



This luminaire contains built-in LED lamps

The lamps cannot be changed in the luminaire.



SYLVANIA 0045165 874/2012