

PORCH SENSE

PORCH SENSE
0053639



Product features

- Battery operated portable light designed for various lighting applications where no suitable electrical socket is available. Uniform light output. Attractive and functional design. Integrated motion and day/night sensor. Low power consumption. IP54 - suitable for roofed outdoor areas. Versatile can be used for a wide range of indoor and outdoor applications like entrance lighting, corridors, balconies, patios, garage. Auto / On / Off switch. 3xAA batteries included.



PRODUCT OVERVIEW

IPC Code	0053639
Product name	PORCH SENSE
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000987
E-number FI	8709903
Fixture luminous flux (lm)	40
Luminaire efficacy (lm/W)	66
Colour temperature (K)	4000
CRI (Ra)	80
Photobiological Risk Group	RG0
Total power consumption (W)	0.6
Electrical protection	Class III
IP rating	IP54
IK rating	IK03
Product EAN number	5410288536392
Lamps	Yes

DATA TABLE

General data

IPC Code	0053639
Product name	PORCH SENSE
Technology	LED
General application	Residential & Consumer
Certifications	EUNEW009
ETIM Class	EC000987
E-number FI	8709903

Optical data

Fixture luminous flux (lm)	40
Luminaire efficacy (lm/W)	66
Colour temperature (K)	4000

PORCH SENSE

PORCH SENSE
0053639

CRI (Ra)	80
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	0.6
Mains voltage (V)	4.5V
Electrical protection	Class III
Drive current (mA)	120

Lifetime data

Lumen maintenance - L70 B50	15000
-----------------------------	-------

Physical data

IP rating	IP54
IK rating	IK03
Nominal Product Length (mm)	105
Nominal Product Width (mm)	59
Nominal Product Height (mm)	76
Weight (kg)	0.2

Packaging


Single packaging type	Carton
Product EAN number	5410288536392
Packaging single length / height (cm)	21.0
Packaging single width (cm)	17.0
Packaging single depth (cm)	22.2
DUN14 (inner)	25410288536396
Units per inner package	6
Packaging inner length / height (cm)	49.0
Packaging inner width (cm)	21.0
Packaging inner depth (cm)	22.2
DUN14 (outer)	15410288536399
Units per outer package	24
Packaging outer length / height (cm)	51.0
Packaging outer width (cm)	44.0
Packaging outer depth (cm)	45.0

Safety data

Safety message	Not Suitable for totally enclosed fixtures
----------------	--

TECHNICAL DRAWINGS

PORCH SENSE *PORCH SENSE* 0053639



SYLVANIA 0053639

 This luminaire contains built-in LED lamps

 } LED

The lamps cannot be changed in the luminaire.


874/2012 

PORCH SENSE PORCH SENSE 0053639



This luminaire contains built-in LED lamps

The lamps cannot be changed in the luminaire.



SYLVANIA 0053639

874/2012