


# Mod. 4209 B

WATERPROOF CASE



METRIC MM-KG-C°



## INTERNAL DIMENSIONS

L LENGTH	420 mm
W WIDTH	300 mm
D DEPTH	95 mm
LID	35 mm
BASE	60 mm


## EXTERNAL DIMENSIONS

L LENGTH	457 mm
W WIDTH	367 mm
D DEPTH	118 mm

## OTHER DATA

WEIGHT EMPTY	2 Kg
WEIGHT WITH FOAM	2.4 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	12 lt
BUOYANCY	6.8 Kg/max
OPERATING TEMPERATURE	°C min -33 / max 90

IMPERIAL IN-LBS-F°



## INTERNAL DIMENSIONS

L LENGTH	16 9/16 in
W WIDTH	11 13/16 in
D DEPTH	3 3/4 in
LID	1 3/8 in
BASE	2 3/8 in

## EXTERNAL DIMENSIONS

L LENGTH	18 in
W WIDTH	14 7/16 in
D DEPTH	4 5/8 in

## OTHER DATA

WEIGHT EMPTY	4.85 lbs
WEIGHT WITH FOAM	5.29 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	3.17 gal
BUOYANCY	14.99 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max 194