


# Mod. 4216 B

PLASTIC RESIN WATERPROOF CASE



METRIC MM-KG-C°



### INTERNAL DIMENSIONS

L LENGTH	420 mm
W WIDTH	300 mm
D DEPTH	160 mm
LID	35 mm
BASE	125 mm


### EXTERNAL DIMENSIONS

L LENGTH	457 mm
W WIDTH	367 mm
D DEPTH	183 mm

### OTHER DATA

WEIGHT EMPTY	2.4 Kg
WEIGHT WITH FOAM	3 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	20 lt
BUOYANCY	14.2 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°



### INTERNAL DIMENSIONS

L LENGTH	16 9/16 in
W WIDTH	11 13/16 in
D DEPTH	6 5/16 in
LID	1 3/8 in
BASE	4 15/16 in

### EXTERNAL DIMENSIONS

L LENGTH	18 in
W WIDTH	14 7/16 in
D DEPTH	7 3/16 in

### OTHER DATA

WEIGHT EMPTY	5.29 lbs
WEIGHT WITH FOAM	6.61 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	5.28 gal
BUOYANCY	31.30 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194