

TOLEDO CANDLE

ToLEDo CANDLE V6 250LM 827 B22 SL
0028397



Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent candle lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- A+ energy rating



PRODUCT OVERVIEW

IPC Code	0028397
Product name	ToLEDo CANDLE V6 250LM 827 B22 SL
Technology	LED
Watt (Rated) (W)	3
Cap/Base	B22
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Certifications	EUTIE103
ETIM Class	EC001959
Luminous flux (lm)	250
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Wattage (W)	3
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288283975

DATA TABLE

General data

IPC Code	0028397
Product name	ToLEDo CANDLE V6 250LM 827 B22 SL
Technology	LED
Watt (Rated) (W)	3
Cap/Base	B22
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
Certifications	EUTIE103
ETIM Class	EC001959

TOLEDO CANDLE

ToLEDo CANDLE V6 250LM 827 B22 SL

0028397

Optical data

Luminous flux (lm)	250
Luminous flux (Rated) (lm)	250
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam angle (Rated) (°)	180
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	3
Equivalent watt (W)	25
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.4
No. Of switching cycles before premature failures	50000
Inrush Current (A)	2
Lamp Energy Label (class)	A+
kWh per 1000 hours burning time	3
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	178
Max. Luminaires per 16A C Breaker	286
Max. Luminaires per 20A C Breaker	358

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	104
Nominal Product Diameter (mm)	35
Weight (kg)	0.028

Packaging

Single packaging type	Carton
Product EAN number	5410288283975
Packaging single length / height (cm)	3.7
Packaging single width (cm)	3.7
Packaging single depth (cm)	10.9
DUN14 (outer)	15410288283972
Units per outer package	6
Packaging outer length / height (cm)	12.0
Packaging outer width (cm)	8.1
Packaging outer depth (cm)	11.5

TOLEDO CANDLE

ToLEDo CANDLE V6 250LM 827 B22 SL
0028397

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Intended purpose	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

