

PRODUCT-DETAILS

# E233-240/60HZ

## E233-240 60HZ WORKING HOUR METER



### General Information

Extended Product Type	E233-240/60HZ
Product ID	2CDE100021R1601
EAN	4016779365901
Catalog Description	E233-240 60HZ WORKING HOUR METER
Long Description	E233-240 60HZ WORKING HOUR METER

### Ordering

EAN	4016779365901
Minimum Order Quantity	1 piece
Customs Tariff Number	90291000

### Dimensions

Product Net Width	17.5 mm
Product Net Height	85 mm
Product Net Depth / Length	58 mm
Product Net Weight	0.064 kg

### Container Information

Package Level 1 Units	10 piece
-----------------------	----------

Package Level 1 Width	93 mm
Package Level 1 Height	74 mm
Package Level 1 Depth / Length	183 mm
Package Level 1 Gross Weight	0.6 kg

## Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

## Additional Information

Accuracy	Reading Accuracy Class 0,01 h
Power Loss	1.5 W
Product Main Type	Hour Counters HMT, E233
Product Name	Hour Counter
Product Range	Elapsed time meter E233
Rated Frequency (f)	50 Hz 60 Hz
Rated Voltage (U <sub>r</sub> )	240 V AC
RoHS Date	0046

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A8017
Declaration of Conformity - CE	2CDK443001D0403
Environmental Information	2CDU400019D0201
Instructions and Manuals	2CSC400002D0208
RoHS Information	2CDK440005K0202

## Classifications

ETIM 4	EC001641 - Hour meter
ETIM 5	EC001641 - Hour meter
ETIM 6	EC001641 - Hour meter
ETIM 7	EC001641 - Hour meter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	7.0 27142313

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Energy Efficiency Devices → Hour Counters

