

PRODUCT-DETAILS

# 432BS6

## Surface inlet, 6h, 32A, IP44, 3P+N+E



### General Information

Extended Product Type	432BS6
Product ID	2CMA193331R1000
EAN	7392696933315
Catalog Description	Surface inlet, 6h, 32A, IP44, 3P+N+E
Long Description	Wall mounted inlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

### Ordering

E-Number (Sweden)	E2417192
E-Number (Finland)	2421524
E-Number (Norway)	1542423
EAN	7392696933315
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

### Dimensions

Product Net Width	85 mm
Product Net Height	116 mm
Product Net Length	163 mm
Product Net Depth / Length	163 mm

Product Net Weight	0.29 kg
Mechanical Drawings	9AKK107680A3014

### Container Information

Package Level 1 Width	188 mm
Package Level 1 Depth / Length	175 mm
Package Level 1 Height	428 mm
Package Level 1 Gross Weight	2.9 kg
Package Level 1 EAN	7392696663311
Package Level 1 Units	box 10 piece
Package Level 2 Units	240 piece

### Technical UL/CSA

Ampere Rating UL/CSA	32 A
Tightening Torque UL/CSA	10.6 in·lb

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1510904
REACH Declaration	2CMC700005D0001

### Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm <sup>2</sup>
Cable Diameter	22 mm
Color	Red
Connection Type	Screw
Degree of Protection	IP44
Design	Surface mounted plug
Frequency (f)	50 Hz 60 Hz
Function	Wall mounted inlet
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#432BS6
Mounting Holes	91x67
Mounting Type	Angled
Number of Poles	5
Order Multiple	10 piece
Product Main Type	EBS
Product Name	Wall mounted inlet
Protection Type	Splashproof
Rated Current (I <sub>n</sub> )	32 A

Rated Frequency (f)	50...60 Hz
Rated Voltage ( $U_r$ )	200/346 ... 240/415 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Surface Inlets
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700002D0001
RAL Number	RAL 7012 - Basalt Grey

---

## Classifications

eClass	27440519
UNSPSC	39121406

---

## Technical

Wire Size	12 ... 10 AWG
Tightening Torque	WireClamp 1.2 N·m

---

## Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Surface Inlets

