

## IP68 Category 6A Cable Joiner



### **IP68 Category 6A Cable Joiner (W78SGpb)**

Our Cat 6A Cable Joiner has been designed for the extension, connection, relocation or repair of copper data cables in harsh environments. Suitable for either internal or external applications, the completed connection is both water and dustproof.

#### **Features:**

- High performance data throughput, easily meets Category 6A data transfer rates at permanent link level
- Backwards compatible – also suitable for use with Cat 5e or Cat 6 cables
- Quick, easy and reliable toolless termination
- Suitable for cables with OD 5.0-8.0mm with core OD 22-26 AWG/0.4-0.76mm
- IP68 rated – water-proof and dustproof (ie can be immersed for up to 30 minutes in water up to 1m depth and dust tight)
- Ideal for use in dusty factories or external environments such as stadiums, marinas and outside plant

#### **Materials:**

- Housing material - Nylon PA66 – high impact resistant and UL 94V-0 flame retardant
- Robust die cast connector casing, supplied with copper foil and cable ties
- Colour: black with orange sealing parts
- Weight: 70 g
- Dimensions: 121.5 mm length x 28 mm diameter



**Packaging:** in individual poly bag then in a bag of 20

**EAN:** 5055386507983

**Commodity Code:** 85177090

06/07/20

ROHS Compliant

Code: W78SG

