

N3172 White Lumina Desk Lamp

The white Lumina Desk Lamp is a sturdy lamp with a flexible goose neck that clamps to the desk. This desk lamp has a modern design that has three brightness levels on three different colour temperatures, making it ideal for crafters, mobile beauty, reading and users with low levels of vision.

Providing a long reach when required but can easily be adjusted to a shorter length by bending the neck.

It comes with a remote control for light adjustment at distance, giving the user the ability to adjust brightness and temperature, as well as turning the light on and off.

The Lumina desk lamp is supplied with a UK plug and is CE certified.

SKU: N3172



Description

Features

- A flexible goose neck, enabling bright light to shine where needed.
- The bright LEDs provides daylight simulation, which is great for colour matching.
- This desk lamp has a 5-step dimmer, with 5 different levels of light temperature.
- Sturdy clamp included for attaching to a desk or other flat surface.

Technical Details

- Head size: 21.5cm x 5.5cm (8.5 inches x 2.25 inches)
- LED size: 13cm x 3.5cm (5 inches x 1.5 inches)
- Maximum height: 111cm (43.75 inches)

- Clamp depth: 5.7cm (2.25 inches)
- Colour temperature: 2800K, 4000K and 6500K
- Total weight: 0.3kg
- Cable length: 190cm (75 inches)
- Colour: White
- Comes with a two-year warranty

You may also like...



N3182 Black Lumina Desk Lamp



N3183 Black Lumina Floor Lamp



N3173 White Lumina Floor Lamp

